

Number of contacts

# 9-50



Stamped solder pins, straight with/without grounding board locks

Identification	No. of contacts	Part No.	
<b>Performance levels</b> Explanations see page 05.04 Other performance levels on request		Performance level 3	Performance level 2
<b>Male connector</b> metal shell with dimples			
Without grounding board locks	9 15 25 37	09 65 121 770 09 65 221 770 09 65 321 770 09 65 421 770	09 65 121 670 09 65 221 670 09 65 321 670 09 65 421 670
With grounding board locks	9 15 25 37	09 65 161 771 09 65 261 771 09 65 361 771 09 65 461 771	09 65 161 671 09 65 261 671 09 65 361 671 09 65 461 671
<b>Female connector</b> metal shell			
Without grounding board locks	9 15 25 37 50	09 66 111 750 09 66 211 750 09 66 311 750 09 66 411 750 09 66 511 750	09 66 111 650 09 66 211 650 09 66 311 650 09 66 411 650 09 66 511 650
With grounding board locks	9 15 25 37	09 66 151 751 09 66 251 751 09 66 351 751 09 66 451 751	09 66 151 651 09 66 251 651 09 66 351 651 09 66 451 651
Please insert digit for flange thread or fitted female screw locks			
M3 ▶ 1 4-40 UNC ▶ 2 fitted screw locks 4-40 UNC ▶ 3 <sup>1)</sup>			

D-Sub

<sup>1)</sup> Fitted screw locks 4-40 UNC not normally kept in stock for performance level 3  
 Connector dimensions see page 05.09. Mating conditions see page 05.04.