



Manual Processing Tool for Cable ties with low profile head

- MK10-SB up to 9.5 mm strap width

The metal MK10-SB tool is ideal for easy handling of the entire HellermannTyton RPE, PE series (Chapter 1.3.). Pre-looped cable ties can be tensioned and cut off flush at the head by pressing the cutting button.



MK10-SB.

Manual Processing Tool for Cable Ties, simple version

- MK20 up to 4.8 mm strap width
- MK21 up to 7.6 mm strap width

Inexpensive alternative to heavy duty tool. Use with HellermannTyton ties up to 7.6 mm wide.

Lightweight design reduces operator fatigue. Simply twist to cut.



MK20, MK21.



Apply.



Tension.



Twist to cut.

Technical Table

Article-No.	Type	Strap Width max. (G)	Strap Thickness max.	Weight (Kg)
110-10001	MK10-SB	9.5	2.5	0.8
110-20006	MK20	4.8	1.5	0.05
110-21016	MK21	7.6	2.5	0.05

All dimensions in mm. Subject to technical changes.