

fast response
high accuracy

pocket
testers



Sturdy compact meter designed for direct sample testing

Easy to read LCD with 0.01 pH resolution

Thin long-reach pH electrode included as standard

- Electrode is quick and easy to replace by unscrewing it from the meter body and adding a new one



Two-point calibration is simple to perform by turning the calibration screws at the top of the tester



Pocket tester with long electrode

Quite simply our best selling pH tester, the Checker 1 is a real favourite with its clear LCD display, long thin pH electrode and ease of operation.

Simple to use, small enough to pop in a pocket and exceptionally well-priced it is an ideal budget-conscious pH tester.

Main benefits

- Fast accurate readings from 0 – 14 pH with a resolution of 0.01 pH
- Small diameter electrode designed to fit easily into a test tube - ideal for laboratory sampling
- 3000 hours of battery life

Electrodes

Checker 1 uses a dedicated small diameter electrode - included as standard.

For replacement electrodes quote part number: HI 1270.

Solutions

We manufacture a wide range of solutions for the care, cleaning and calibration of your electrodes.

Specifications

Product Code	HI 98103
Range	0.00 to 14.00 pH
Resolution	0.01 pH
Accuracy	±0.2 pH
Calibration	manual, 1 or 2 points
Battery Type / Life	2 x 1.5V / approx. 3000 hours of continuous use
Electrode	HI-1270 (included)
Environment	0 to 50°C : RH max 95%
Dimensions	66 x 50 x 25 mm - without probe
Weight	50 g

Ideal for

- Use in education
- Low budget applications
- Quick check and general laboratory use
- Laboratory sampling

