

**SP 204SN  
SP 204SFN**

**Black-and-white Multifunction Printer**

Copier  Printer  facsimile  Scanner



**SP 204SN**

22  
ppm B/W

**SP 204SFN**

22  
ppm B/W

## A desktop MFP running at a fast 22 cpm

In need of increased productivity for your home/small office? The new B/W Laser multifunction printers SP 204SN/SP 204SFN are compact enough to fit on your desktop, yet packed with print, scan and fax features (SP 204SFN). You are off to a flying start with a fast print speed of 22 pages per minute. Remarkably easy to operate, your device comes network-ready and is guaranteed to provide many years of service.



### Productive and efficient

With a short warm-up time of less than 25 seconds and a fast print speed of 22 pages per minute, these devices will boost your office productivity. The paper tray takes 150 sheets. Manual duplex enhances productivity and saves paper.



### Easy to operate

The SP 204SN/SP 204SFN are designed for ease of use. The clear, 2-line LCD operation panel provides easily readable instructions. Print status is clearly visible at all times.



### Create professional documentation

Print at a resolution of 1,200 dpi to create professional-looking documents. Scan in high-resolution colour. Email scans, or send them directly to a PC. Copy both sides of an ID card onto one side of paper. Print with an embedded watermark.

# Transform your office productivity and reduce costs



## Budget-friendly

The long-lasting, high-yield, All-in-One toner cartridge reduces operating cost. This makes these devices affordable investments for cost-conscious home and small offices.

## Compact and reliable

Take advantage of their small footprint and simply place the SP 204SN/ SP 204SFN on your desktop. In addition, these devices are robust and durable for many years of reliable use.



## Built-in networking and faxing

Enjoy seamless network integration thanks to the standard built-in Network Interface Card. Fax quickly and efficiently with the Super G3 modem (SP 204SFN).

## Environmentally responsible

At Ricoh we help you lower your environmental footprint. The SP 204SN/ SP 204SFN include environmentally responsible features such as a short warm-up time and increased toner yield.



# SP 204SN/SP 204SFN

## MAIN SPECIFICATIONS

### GENERAL

Warm-up time:	25 seconds
First output speed:	10 seconds
Continuous output speed:	22 pages per minute
Dimensions (W x D x H):	402 x 360 x 291 mm
Weight:	9.9 kg
Power source:	220 - 240 V, 50/60 Hz

### COPIER

Copying process:	Laser beam scanning and electro-photographic printing
Multiple copying:	Up to 99 copies
Resolution:	600 x 600 dpi
Zoom:	From 25% to 400% in 1% steps

### PRINTER

RAM:	32 MB
Printer language:	Standard: DDST (GDI)
Print resolution:	1,200 x 600 dpi
Interface:	USB 2.0, Ethernet 10 base-T/100 base-TX
Network protocol:	TCP/IP
Windows® environments:	Windows® XP, Windows® Vista, Windows® 7, Windows® 8, Windows® Server 2003, Windows® Server 2008, Windows® Server 2008R2, Windows® Server 2012

### SCANNER

Scanning speed:	Full colour: Maximum 6.5 originals per minute B/W: Maximum 13 originals per minute
Resolution:	Maximum: 600 dpi
Original size:	A4
Bundled drivers:	Network TWAIN
Scan to:	E-mail, Folder, USB

### FAX (SP 204SFN)

Circuit:	PSTN, PBX
Compatibility:	G3
Transmission speed:	3 second(s)
Modem speed:	Maximum: 33.6 Kbps

### PAPER HANDLING

Recommended paper size:	Standard paper tray(s): A4, A5, A6, B5, B6 Bypass tray: A4, A5, A6, B5, B6
Paper input capacity:	Maximum: 151 sheets
Paper output capacity:	Maximum: 50 sheets
Paper weight:	Standard paper tray(s): 60 - 105 g/m <sup>2</sup> Bypass tray: 60 - 105 g/m <sup>2</sup>

### ECOLOGY

Power consumption:	Maximum: 400 W Sleep mode: 5 W
--------------------	-----------------------------------

### SOFTWARE

Standard:	Web Status Monitor
-----------	--------------------

### CONSUMABLES

All-in-one cartridge capacity (low yield):	Black: 1,500 prints
All-in-one cartridge capacity (high yield):	Black: 2,600 prints

Copy speed Germany: 14 cpm; Belgium, Austria: 9 cpm.  
Consumable yield measuring method ISO/IEC 19752.

For availability of models, options and software, please consult your local Ricoh supplier.



ISO9001 certified, ISO14001 certified, ISO27001 certified

All brand and/or product names are trademarks of their respective owners.

Specifications and external appearance are subject to change without notice. The colour of the actual product may vary from the colour shown in the brochure. The images in this brochure are not real photographs and slight differences in detail might appear.

Copyright © 2013 Ricoh Europe PLC. All rights reserved. This brochure, its contents and/or layout may not be modified and/or adapted, copied in part or in whole and/or incorporated into other works without the prior written permission of Ricoh Europe PLC.

[www.ricoh-europe.com](http://www.ricoh-europe.com)

**RICOH**  
imagine. change.