

CAB CAB PC 203018 T



Order symbol: CAB PC 203018 T
Product nbr: 8113031
Description: Cabinet, PC
Remarks: Latch on the short side

EAN: 6418074020031
EI. number:
 Finland: 3424153
 Denmark: 8212020414
 Italy: 7822010
 Sweden: 2539937
 Norway:

Including: Cabinet base, door with EPDM gasket, latches, screws for mounting plate/DIN-rail and corner plugs.

Sample photo

Dimensions:		Length	Width	Height	Rating:
mm:		300	200	180	Ingress Protection (EN 60529): IP 65
inch:		11.8	7.9	7.1	Impact Resistance (EN 62262): IK 08
Materials:					Electrical insulation: Totally insulated
Material:		Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			UV resistance: UL 508
Cover colour:		Smoked grey			Flammability Rating (UL 746 C 5): UL 746C 5V
Gasket material:		EPDM			Glow Wire Test (IEC 695-2-1) °C: 960
Temperatures:					UL Type: UL TYPE 1, 4, 4X, 12, 13
Short term:		-40 ... 120 °C			Certificates:
Continuous:		-40 ... 80 °C			Germanischer Lloyd (GL)
Short term:		-40 ... 250 °F			Underwriters Laboratories
Continuous:		-40 ... 175 °F			Fimko
Accessories:					Lloyds Register of Shipping (LR)
EKIV 23		Mounting plate			Europe EN 62208: 2003
EKIV 17		DIN-35 Mounting rail			UL Canada
DS35170E1		DIN-35 Mounting rail			Gost R
EKIV 27		DIN-35 Mounting rail			
DS35270E1		DIN-35 Mounting rail			
FP A 23		Swing-out door/Front plate			
MB 12225 AL		Swing door set			
FP 23		Front plate			
FP 12-23		Front plate			
DRF 23		DIN rail frame set			

