

**UL PICCOLO UL PC D 85 G**



Sample photo

**Order symbol:** UL PC D 85 G  
**Product nbr:** 8714308  
**Description:** UL Enclosure, PC  
**Remarks:** Grey cover

**EAN:** 6418074038913  
**EI. number:**  
Finland:  
Denmark: 8212031115  
Italy: 7201035U  
Norway:

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:				Length	Width	Height	Rating:
<b>mm:</b>		170	80	85	Ingress Protection (EN 60529): IP 66/67		
<b>inch:</b>		6.7	3.1	3.3	Impact Resistance (EN 62262): IK 08		
<b>Materials:</b>							
<b>Material:</b>	Polycarbonate			Electrical insulation: Totally insulated			
<b>Base colour:</b>	RAL 7035			Halogen free (DIN/VDE 0472, Part 815): Yes			
<b>Cover colour:</b>	RAL 7035			UV resistance: UL 508			
<b>Cover screws material:</b>	Polyamide			Flammability Rating (UL 746 C 5): UL 746C 5V			
<b>Cover screws colour:</b>	Grey			Glow Wire Test (IEC 695-2-1) °C: 960			
<b>Gasket material:</b>	Polyurethane			UL Type: UL TYPE 1, 4X, 6, 12, 13			
<b>Temperatures:</b>							
<b>Short term:</b>	-40 ... 120 °C			Certificates:			
<b>Continuous:</b>	-40 ... 80 °C			Germanischer Lloyd (GL)			
<b>Short term:</b>	-40 ... 250 °F			Underwriters Laboratories			
<b>Continuous:</b>	-40 ... 175 °F			Fimko			
<b>Accessories:</b>							
				Europe EN 62208: 2003			
				UL Canada			
				Gost R			

PICCOLO 170x80x65-85

