

# Fibreglass Enclosures IP65



Spelsberg's range of high quality GRP (Glass Reinforced Polyester) enclosures offer the very best in style and protection and come with a host of user friendly accessories.

GRP enclosures offer effective corrosion resistance for electrical and electronic controls in harsh environments including Marine, Off-shore Petrochemical/ Paper plants and Water Treatment Facilities.

All GRP enclosures offer a robust construction with integral drip shield for directing liquids away from the door seal as well as a standard Triangular insert for increased security. Optional Key Locks are available. 7 Popular standard sizes are available.

A stylised window door version is also available providing easy visual inspection of interior components.

**Material/Surface Finish**  
Enclosure and door made from fibreglass-reinforced Polyester. Window door produced with impact resistant 3.0mm acrylic bonded with IP65 Seal.

Mounting plates from 2.5mm sheet steel (galvanised) Enclosure RAL7035


## Key Features Overview

- Sealed to IP65
- 7 Standard popular sizes available  
250 x 300 x 170mm up to  
810 x 1060 x 350mm (WxHxD)
- Easy install accessories - mounting plates, inner doors, modular kits
- Hinging allowing 240 degree door opening. Left or right mounting
- Integral drip shields moulded as standard
- Impact resistant polycarbonate window is permanently bonded in place
- Moulded in mounting rails for installation of inner doors and modular kits
- Standard colour - RAL 7035

## Product Overview and Size Range



Dimensions (W X H X D)	Plain door	Glazed door	Metal MTG Plate	Polyester MTG Plate	Inner door	Modular Frame with Slot	Module Frame Blank
265x300x165	E-FG04601	E-FG04621G	E-MP04670	EPP-04690			
325x425x180	E-FG04602	E-FG04622G	E-MP04671	EPP-04691	E-ID04631	EMF-04640	EBP-04645
430x500x210	E-FG04603	E-FG04623G	E-MP04672	EPP-04692	E-ID04632	EMF-04641	EBP-04646
430x650x210	E-FG04604	E-FG04624G	E-MP04673	EPP-04693	E-ID04633	EMF-04641	EBP-04646
540x650x260	E-FG04605	E-FG04625G	E-MP04674	EPP-04694	E-ID04634	EMF-04642	EBP-04647
615x805x315	E-FG04606	E-FG04626G	E-MP04675	EPP-04695	E-ID04635	EMF-04643	EBP-04648
810x1060x350	E-FG04608	E-FG04628G	E-MP04677		E-ID04637	EMF-04644	EBP-04649



Dimensions (W X H X D)	Module frame Double Blank	DIN Rail assembly	Vertical mounting frame	Plate adjustment brackets (1)*	Cover strip for modular frame (3)*	Key lock	Wall brackets galvanised	Wall brackets stainless
265x300x165						E-KL04681	E-MB04680	E-MB04688
325x425x180	EBPD-04696	EDR-04660	EVF-04651	EPAB-04682	ECS-05180	E-KL04681	E-MB04680	E-MB04688
430x500x210	EBPD-04697	EDR-04661	EVF-04652	EPAB-04682	ECS-05180	E-KL04681	E-MB04680	E-MB04688
430x650x210	EBPD-04697	EDR-04661	EVF-04653	EPAB-04682	ECS-05180	E-KL04681	E-MB04680	E-MB04688
540x650x260	EBPD-04698	EDR-04662	EVF-04653	EPAB-04682	ECS-05180	E-KL04681	E-MB04680	E-MB04688
615x805x315	EBPD-04699	EDR-04663	EVF-04654	EPAB-04682	ECS-05180	E-KL04681	E-MB04680	E-MB04688
810x1060x350	EBPD-04679	EDR-04664	EVF-04655	EPAB-04682	ECS-05180	E-KL04681	E-MB04680	E-MB04688

