

MNX PC 125/50 LT



Sample photo

Order symbol: PC 125/50 LT
Product nbr: 6012908
Description: Enclosure, PC
Remarks: Smoked transparent cover

EAN: 6418074014016
EI. number:
 Finland: 3420432
 Denmark: 8212022564
 Italy: 7352043
 Sweden: 6012908
 Norway:

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		130	130	50	Ingress Protection (EN 60529): IP 66/67
inch:		5.1	5.1	2.0	Impact Resistance (EN 62262): IK 08
Materials:					
Material:		Polycarbonate			
Base colour:		RAL 7035			
Cover colour:		Smoked grey			
Cover screws material:		Polyamide			
Cover screws colour:		Black			
Gasket material:		TPE			
Temperatures:					
Short term:		-40 ... 120 °C			
Continuous:		-40 ... 80 °C			
Short term:		-40 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
MIV 125		Mounting plate (Galvanized steel)			
MIN 10		DIN-15 Mounting rail			
MIV 10		DIN-35 Mounting rail			
FP A 125/130		Front plate (Aluminium)			
HFP 130		Front plate hinge series			
FP 22046		Wall fastening lug (4 pcs)			
					Certificates:
					Germanischer Lloyd (GL)
					Underwriters Laboratories
					Det Norske Veritas
					Fimko
					Europe EN 62208: 2003
					UL Canada
					Gost R
					NEMA Class: NEMA 1, 4, 4X, 6
					Electrical insulation: Totally insulated
					Halogen free (DIN/VDE 0472, Part 815): Yes
					UV resistance: UL 508
					Flammability Rating (UL 746 C 5): UL 746C 5V
					Glow Wire Test (IEC 695-2-1) °C: 960

