



Sample photo

Order symbol: PCT 122008
Product nbr: 7022761
Description: Enclosure, PC
Remarks: Transparent cover

EAN: 6418074003799
EI. number:
 Finland: 3423538
 Denmark: 8212002856
 Italy: 7302045
 Sweden: 7022761
 Norway: 2536614

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		200	120	75	Ingress Protection (EN 60529): IP 66/67
inch:		7.9	4.7	3.0	Impact Resistance (EN 62262): IK 08/07
Materials:					Electrical insulation: Totally insulated
Material:		Polycarbonate		Halogen free (DIN/VDE 0472, Part 815): Yes	
Base colour:		RAL 7035		UV resistance: UL 508	
Cover colour:		Clear transparent		Flammability Rating (UL 746 C 5): UL 746C 5V	
Cover screws material:		Stainless steel		Glow Wire Test (IEC 695-2-1) °C: 960	
Gasket material:		Polyurethane		NEMA Class: NEMA 1, 4, 4X, 12, 13	
Temperatures:					Certificates:
Short term:		-40 ... 120 °C		Underwriters Laboratories	
Continuous:		-40 ... 80 °C		Fimko	
Short term:		-40 ... 250 °F		Europe EN 62208: 2003	
Continuous:		-40 ... 175 °F		UL Canada	
Accessories:					Gost R
TM 1220		Mounting plate			
MIV 10		DIN-35 Mounting rail			
TRH 1220		DIN-35 Mounting rail			
TF 28037		Wall fastening lug (4 pcs)			
TH A		Grey plastic hinges (2 pcs)			

