

EURONORD PCT 162513



Sample photo

Order symbol: PCT 162513
Product nbr: 7022861
Description: Enclosure, PC
Remarks: Transparent cover

EAN: 6418074003812
EI. number:
 Finland: 3423542
 Denmark: 8212002979
 Italy: 7302055
 Sweden: 7022861
 Norway: 2536618

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		250	160	125	Ingress Protection (EN 60529): IP 66/67
inch:		9.8	6.3	4.9	Impact Resistance (EN 62262): IK 08/07
Materials:					Electrical insulation: Totally insulated
Material:		Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			UV resistance: UL 508
Cover colour:		Clear transparent			Flammability Rating (UL 746 C 5): UL 746C 5V
Cover screws material:		Stainless steel			Glow Wire Test (IEC 695-2-1) °C: 960
Gasket material:		Polyurethane			NEMA Class: NEMA 1, 4, 4X, 12, 13
Temperatures:					Certificates:
Short term:		-40 ... 120 °C			Underwriters Laboratories
Continuous:		-40 ... 80 °C			Fimko
Short term:		-40 ... 250 °F			Europe EN 62208: 2003
Continuous:		-40 ... 175 °F			UL Canada
Accessories:					Gost R
TM 1625		Mounting plate			
TRM 0816		DIN-15 Mounting rail			
TRH 1216		DIN-35 Mounting rail			
TRH 24		DIN-35 Mounting rail			
TF 28037		Wall fastening lug (4 pcs)			
TH A		Grey plastic hinges (2 pcs)			

