

UL MNX UL PC 175/100 HG



Sample photo

Order symbol: UL PC 175/100 HG
Product nbr: 6411321
Description: UL Enclosure, PC
Remarks: Grey cover

EAN: 6418074014450
EI. number:
 Finland:
 Denmark: 8212030530
 Italy: 7351115U
 Norway:

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		180	180	100	Ingress Protection (EN 60529): IP 66/67
inch:		7.1	7.1	3.9	Impact Resistance (EN 62262): IK 08
Materials:					Electrical insulation: Totally insulated
Material:		Polycarbonate		Halogen free (DIN/VDE 0472, Part 815): Yes	
Base colour:		RAL 7035		UV resistance: UL 508	
Cover colour:		RAL 7035		Flammability Rating (UL 746 C 5): UL 746C 5V	
Cover screws material:		Polyamide		Glow Wire Test (IEC 695-2-1) °C: 960	
Cover screws colour:		Grey		UL Type: UL TYPE 1, 4, 4X, 6, 12, 13	
Gasket material:		TPE			
Temperatures:					Certificates:
Short term:		-40 ... 120 °C		Germanischer Lloyd (GL)	
Continuous:		-40 ... 80 °C		Underwriters Laboratories	
Short term:		-40 ... 250 °F		Det Norske Veritas	
Continuous:		-40 ... 175 °F		Fimko	
Accessories:					Europe EN 62208: 2003
					UL Canada
					Gost R

