

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [19004-0009](#)
Status: **Active**
Description: InsulKrimp™ Fully Insulated Coupler, Male, for 10-12 AWG Wire, Box

Documents:

[Drawing \(PDF\)](#) [Product Specification PS-19902-013 \(PDF\)](#)
[Product Specification PS-19902-008 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-19902-011 \(PDF\)](#)

Agency Certification

CSA LR18689
 UL E79133

General

Product Family Quick Disconnects
 Series [19004](#)
 Crimp Quality Equipment Yes
 Insulated Fully
 MolexKits Yes
 Product Name InsulKrimp™
 Type Quick Disconnect
 UPC 800753030138

Physical

Barrel Type Closed
 Color - Resin Yellow
 Flammability 94V-2
 Gender Male
 Glow-Wire Compliant No
 Insulation Nylon (PA)
 Lock to Mating Part None
 Material - Metal Brass
 Material - Plating Mating Zinc Chromate
 Material - Plating Termination Zinc Chromate
 Material - Resin Nylon
 Net Weight 1.978/g
 Orientation Straight
 Packaging Type Bag
 Polarized to Mating Part No
 Tab Thickness 0.81mm
 Tab Width 6.35mm
 Temperature Range - Operating -65°C to +105°C
 Wire Insulation Diameter 6.99mm max.
 Wire Size AWG 10, 12
 Wire Size mm² 3.30 - 5.00

Electrical


Voltage - Maximum 600V

Material Info

Old Part Number C-2264

Reference - Drawing Numbers

Product Specification PS-19902-008, PS-19902-011, PS-19902-013
 Sales Drawing SD-19004-002



EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[19004Series](#)

Use With

[19005-0010](#) , [19005-0014](#) , [19005-0015](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool	0640015100
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640055100

This document was generated on 10/21/2013

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION