

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [74547-0301](#)
Status: **Active**
Overview: iPass™ Connector System
Description: External iPass Mini Multi-Lane SAS X4 Cable Assembly, 26 Circuits, 28 AWG, 1.0m Length, Key 2, 4, 6

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Test Summary TS-74547-001 \(PDF\)](#)

Agency Certification

CSA LR64395
 UL E72548

General

Product Family Cable Assemblies
 Series [74547](#)
 Comments Universal Key, SAS
 Connector to Connector Mini SAS-to-Mini SAS
 Overview [iPass™ Connector System](#)
 Product Name iPass™, Mini Multi-Lane, SAS, X4
 UPC 822350284455

Physical

Cable Length 1.0m
 Circuits (Loaded) 26
 Gender Male-Male
 Lock to Mating Part Yes
 Material - Metal Stainless Steel
 Net Weight 156.187g
 Packaging Type Bag
 Pitch - Mating Interface 0.80mm
 Single Ended No
 Wire Insulation Diameter N/A
 Wire Size AWG 28
 Wire/Cable Type Parallel Pair


Electrical

Current - Maximum per Contact 1A
 Shielded Yes
 Voltage - Maximum 30V

Material Info

Reference - Drawing Numbers

Sales Drawing SD-74547-100
 Test Summary TS-74547-001



EU RoHS

**ELV and RoHS
 Compliant**
**REACH SVHC
 Contains SVHC: No
 Low-Halogen Status
 Not Reviewed**

China RoHS



**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series

[74547Series](#)

Mates With

[75586](#) iPass™ Receptacle. [74548](#) EMI
 Housing Assembly

Use With

[74735](#) X2 Transceiver. [74739](#) XPAK
 Transceiver. [74548](#) External iPass Mini
 Multi-Lane SAS Guide Frame