


VECTORBORD® CIRCBOARD®Part No. : 8018**Description :**

100 mm x 160 mm, Hole Dia.: 0.6 mm, Grid: 2 mm x 2 mm
Pad-Per-Hole. 2mm Grid Pattern : Q & P
Combination Pattern: half 2mm grid & half 0.1" grid
Dual copper rows in middle for Vcc/Gnd use
Eurocard size: 100mm x 160mm
100mm height accepts cPCI 2 mm J1 (25 row) & J2 (22 row) connectors on edge
Plated Thru Holes with annular ring
Pads on both sides J2 (22 holes) J1 (25 holes)



Circuit Pattern :	Pad-Per-Hole & 2mm, Grid Pattern : " Q & P " pattern
Contacts :	N/A
Hole Diameter :	0.6 mm +/- 0.05 { 0.025" +/- 0.002} & 0.042"
Grid :	2 mm x 2 mm & 0.100 x 0.100 { Combo 0.1" & 2 mm }
Dimension { H, W, T } :	100 mm x 160 mm x 1.575 mm { 3.94" x 6.30" x 0.062" }
Material :	FR4 Epoxy Glass { MIL - P13949 type Gf }
Solder Terminals :	0.025" Dia. K36 .. & ... 0.042" Dia. ... T42-1, T46, T49, T68
Wire-Wrap Connector :	2 mm (Call Factory)
NEMA Grade :	FR4
UL Flammability Class :	94V - 0

email us your requirements : inquire@vectorelect.com

11115 Vanowen St., North Hollywood, CA 91605, USA

Tel.: (818) 985 8208, (800) 423 5659; Fax : (818) 985 7708

Circbord®, Vectorbord® and VectorPak® are registered trademarks of Vector Electronics & Technology, Inc.
CompactPCI® is a registered trademark of PCIMG. © 2001 Vector Electronics & Technology, Inc. - All Rights Reserved