

EHM007

MMJ STRAIGHT THROUGH CABLE

Status: Available

FUNCTIONAL NOTES:

THIS IS A STRAIGHT THROUGH MMJ TO MMJ CABLE USED IN SOME DEC APPLICATIONS.

PRODUCT SPECIFICATIONS:

Physical	
Connector One	MMJ
Connector Two	MMJ
Application	MMJ straight pinned cable used with DEC equipment
Diameter	0.10 +/- 0.005"
Wire Gauge	26 awg
Twist Per Foot	None
Supported Distance	50 ft
Shielding	None
Mutual Capacitance	22 PF/FT
Resistance	45 OHMS/1000 FT.
Jacket Material	PVC
Jacket Thickness	0.032"
Conductor Material	STRANDED COPPER
Number of Conductors	6 conductors 7 strands per conductor
Hood Assembly	PLASTIC MMJ
Literature	
Manual Available?	NO
Schematic Vendor Name	SPACE SHUTTLE
Schematic Available?	YES
Schematic Non-Disclosure Required?	YES
Schematic Date	DECEMBER 08, 1994
Agency Compliance	
N.E.C. Code	UL E129760 TYPE CM 75 CELSIUS AWM 20251