


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [39-00-0048](#)
Status: **Active**
Overview: Mini-Fit Jr.™ Power Connectors
Description: Mini-Fit® Male Crimp Terminal, Tin (Sn) over Plated Brass Contact, 22-28 AWG, Reel

Documents:

Drawing (PDF)	Product Specification PS-52034-004 (PDF)
Product Specification PS-51010-005 (PDF)	Product Specification PS-5556-002 (PDF)
Product Specification PS-51010-006 (PDF)	Packaging Specification PK-5558-001 (PDF)
Product Specification PS-51096-001 (PDF)	Test Summary TS-5556-002 (PDF)
Product Specification PS-52034-003 (PDF)	RoHS Certificate of Compliance (PDF)



General

Product Family	Crimp Terminals
Series	5558
Application	Power
Crimp Quality Equipment	Yes
Overview	Mini-Fit Jr.™ Power Connectors
Product Name	Mini-Fit®
UPC	800753584617

Physical

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.154/g
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.889µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.90-1.80mm
Wire Size AWG	22, 24, 26, 28
Wire Size mm²	N/A

Electrical

Current - Maximum per Contact	9A
Voltage - Maximum	600V

Material Info

Old Part Number	5558T2
-----------------	--------

Reference - Drawing Numbers

Packaging Specification	PK-5558-001
Product Specification	PS-51010-005, PS-51010-006, PS-51096-001, PS-52034-003, PS-52034-004, PS-5556-002, RPS-30067-002
Sales Drawing	SD-5558****
Test Summary	TS-5556-002

EU RoHS ELV and RoHS Compliant REACH SVHC Contains SVHC: No Low-Halogen Status Low-Halogen	China RoHS 
---	--

Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[5558Series](#)

Mates With

[5556](#) Mini-Fit® Crimp Terminal

Use With

[5559](#) Mini-Fit Jr.™ Plug Housing, [30068](#) Mini-Fit® TPA Plug Housing, [42475](#) Mini-Fit® BMI Plug Housing

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
FineAdjust™ Applicator for Insulation OD 1.10-1.30mm - 22-28 AWG Extraction Tool	0639020200 0011030044

Hand Crimp Tool for	<u>0638191000</u>
Crimp Terminals	
FineAdjust™	<u>0639002700</u>
Applicator for	
Insulation OD	
1.30-1.50mm - 22-28	
AWG	
FineAdjust™	<u>0639023800</u>
Applicator for	
Insulation OD	
0.95-1.08mm - 22-28	
AWG	
T2 Terminator™	<u>0639102700</u>
for insulation OD	
1.30-1.50mm - 22-28	
AWG	
T2 Terminator™	<u>0639120200</u>
for insulation OD	
1.10-1.30mm - 22-28	
AWG	
T2 Terminator™	<u>0639123800</u>
for insulation OD	
0.95-1.08mm - 22-28	
AWG	
Japan	
Description	Product #
Hand Extraction Tool	<u>0570316000</u>
Applicator for M21 1A	<u>0570383000</u>
Bench Press, 22-28	
AWG Wire	

This document was generated on 10/21/2013

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION