

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [88768-5400](#)  
**Status:** **Active**  
**Overview:** [DMS-59®](#)  
**Description:** 1.27mm Pitch DMS-59® -to-DVI-I(F)+VGA(F) Adapter Cable Assembly, 0.20m Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family Cable Assemblies  
 Series [88759](#)  
 Connector to Connector DMS-59™-to-DVI-/VGA  
 Overview [DMS-59®](#)  
 Product Name DMS59®  
 UPC 756054581636

**Physical**

Cable Length 0.20m  
 Circuits (Loaded) 59  
 Color - Resin Black  
 Gender Male-Female  
 Lock to Mating Part Yes  
 Material - Metal Aluminum, Phosphor Bronze, Steel  
 Material - Plating Mating Gold, N/A  
 Material - Plating Termination Tin  
 Material - Resin High Temperature Thermoplastic, Low Density Polyethylene  
 Net Weight 138.530/g  
 Packaging Type Bag  
 Pitch - Mating Interface 1.27mm  
 Plating min - Mating 0.051µm, 0.762µm, 1.905µm  
 Plating min - Termination 2.540µm, 3.810µm  
 Single Ended No  
 Termination Interface: Style N/A, Through Hole  
 Wire Insulation Diameter N/A  
 Wire Size AWG 32  
 Wire/Cable Type Round


**Electrical**

Current - Maximum per Contact 1A  
 Impedance 100#  
 Shielded Yes  
 Voltage - Maximum 30V AC

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing SD-88744-098



**EU RoHS**

**RoHS Compliant by Exemption**  
**REACH SVHC Not Reviewed**  
**Low-Halogen Status Not Reviewed**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[88759Series](#)