

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [19072-0073](#)
Status: **Active**
Description: VibraKrimp™ Ring Tongue Terminal for 16 - 14 AWG Wire, Stud Size 10 (M5), Length 16.69mm

Documents:

Drawing (PDF)	Product Specification PS-19902-013 (PDF)
Product Specification PS-19902-011 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR18689
UL	E32244

General

Product Family	Ring and Spade Terminals
Series	19072
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Product Name	VibraKrimp™
Type	Ring
UPC	800753074316

Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	0.889/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Stud Size	10 (M5)
Wire Size AWG	14, 16

Material Info

Old Part Number	BB-437-10
-----------------	-----------

Reference - Drawing Numbers

Product Specification	PS-19902-011, PS-19902-013
Sales Drawing	BBCD40101

EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[19072Series](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Crimp Hand Tool	0640016800
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640056800

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION