

# Aluminum Service Poles

## Ordering Information, Specifications and Dimensions



HBLPP10AI



HBLPP10IGA




HBLPP10SAI



ATB



PPTRIM1



### Aluminum Series Offering

Hubbell offers a line of gray, ivory and clear anodized aluminum service poles. These attractive and durable poles effectively distribute power and telecommunications wiring from above the ceiling to workstations below. They are offered in lengths of 10' 2", 12' 2", and 15' 2" with a variety of electrical wiring devices. Poles with three service capability have a divider to separate power and low voltage wiring.

A blank pole with knockouts is also offered which does not have devices or wiring. In addition to a standard pole, which has two 20 amp duplex receptacles, an isolated ground or surge suppression version is also available. All poles, except the blank versions, are factory wired with Hubbell Style Line® decorator receptacles. Two Style Line® knockouts are also provided on the same side as the power receptacles for communication outlets.

### Ordering Information

Aluminum service poles; gray or ivory painted and clear anodized aluminum; Style Line® decorator duplex receptacles and two Style Line® knockouts for communications; includes ceiling trim mounting plate and scuff boot.

Description	Height Feet (m)	Catalog Number		Clear Anodized Aluminum
		Gray	Ivory	
Three service; two 20A 125V Style Line® duplex receptacles; one circuit.	10' 2" (3.10m)	<b>HBLPP10A</b>	<b>HBLPP10AI</b>	<b>HBLPP10AAL</b>
	12' 2" (3.71m)	<b>HBLPP12A</b>	<b>HBLPP12AI</b>	<b>HBLPP12AAL</b>
	15' 2" (4.62m)	<b>HBLPP15A</b>	<b>HBLPP15AI</b>	<b>HBLPP15AAL</b>
Three service; one orange isolated ground 20A 125V Style Line® duplex receptacle; one 20A 125V Style Line® duplex receptacle; two circuits.	10' 2" (3.10m)	<b>HBLPP10IGA</b>	<b>HBLPP10IGA I</b>	—
Three service; two orange isolated ground 20A 125V Style Line® duplex receptacles; one isolated ground surge suppression 20A 125V duplex receptacle; one circuit.	10' 2" (3.10m)	<b>HBLPP10SA</b>	<b>HBLPP10SA I</b>	—
Three service; blank pole; divider;	10' 2" (3.10m)	<b>HBLPPOA</b>	<b>HBLPPOAI</b>	<b>HBLPPOAAL</b>
	12' 2" (3.71m)	<b>HBLPPO12A</b>	<b>HBLPPO12AI</b>	<b>HBLPPO12AAL</b>
	15' 2" (4.62m)	<b>HBLPPO15A</b>	<b>HBLPPO15AI</b>	<b>HBLPPO15AAL</b>
Adjustable T-bar assembly for mounting poles in the middle of ceiling tile (req. PPTRIM1 trim kit).		<b>ATB</b>	<b>ATB</b>	<b>ATB</b>
Replacement service pole trim kit (office white).		<b>PPTRIM1</b>	<b>PPTRIM1</b>	<b>PPTRIM1</b>

Note: See section W for additional information on datacom products.

### Specifications

Material: Extruded aluminum; .05" thick (1.27mm)  
 Finish: gray, ivory or clear anodized aluminum  
 Conductors: #12 AWG stranded copper  
 Receptacles: (see drawings below)  
 Listing: UL Listed

Wiring Capacity (@40% fill)	Voice Data Channel*			Power Channel**
	Cat. 5e	Cat. 6	Cat. 6A	
HBLPP10A; HBLPP12A; HBLPP15A; HBLPP10IGA	26	11	9	41
HBLPPO10A; HBLPPO10SAI	8	6	3	41
HBLPPOA, HBLPPO12A, HBLPPO15A (with barrier)	26	11	9	41

Note: \*Pole wiring capacity (telephone fill): Cat. 5 UTP (1.96 sq. ft.).  
 \*\*#12 THHN stranded.

### Dimensions

