



Sta-Kon®

Ring Terminal
T&B Catalog Number:

UPC Number:
Status:
Description:

RE6-14
 78621087863
 Active

Insulated Nylon Ring Terminal For Wire Range 6 Stud Size 1/4, Blue
WEB_USE

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

Features

Funneled Barrel Entry, Deep Internal Serrations, Brazed or overlapping seams.

General

Insulation Type	Insulated Nylon
Terminal Series	RE
Material	Copper
Finish	Electro -Tin Plated
Color	Blue
Wire Range	6
Stud Size	1/4

Dimension Information

Maximum Insulation (inches)	.420
Stock Thickness	.04
A (inches)	1.65
B (inches)	.49
C (inches)	.28
M (inches)	1.40

Specifications

Temperature Rating	105°C
Voltage Rating	600V
Flammability Rating	UL 94 V-2

Tooling

Tool Charts	Available on Website
Application Tools	ERG4007
Recommended Tool	ERG4007

Packaging

T&B Order Multiple	20
T&B Inner Pack	20
Package in Units	200
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	1.45 lbs. per 100
Alternate Package Qty	RE717

Application Support

Overview	Available on Website
Wire Guide Tables	Available on Website

Notes

Not available on Mylar Tape.

Certifications

RoHS Compliance

Yes

Certifications



File Nbr:

E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com