



Ty-Rap®

**Standard
T&B Catalog Number:**

TY29MX

UPC Number:

78621083068

Status:

Active

Description:

Cable Tie 120lb 30" Ultraviolet Resistant Black Nylon with Stainless Steel Locking Device Bulk Pack, Military Specified (MIL-SPEC MS3367-6-0)

Features

Oval low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time. Because there are no notches, Ty-Rap ties provide an infinite number of locking positions while fastening the tie at the precise bundle diameter needed.

The Turned-up Tail orients the tie for easy assembly, making the ties easier to pick up on a flat surface. The No-Slip Tail provides easy grip during tensioning. Ty-Rap ties feature a unique friction surface designed to reduce slippage during installation.

Smooth, notchless body reduces stress concentration points under tension, making the tie stronger and lower profile than notched body ties. Ribbed and Stippled body grips the bundle and prevents slippage. Rounded edges protect insulation, preventing sharp edges from damaging cables.

General

Material	Nylon 6.6 Weather Resistant
Color	Black

Dimension Information

Nominal Length (inches)	30
Length (inches)	30
Width (inches)	.270
Max. Wire Bundle Diameter (inches)	9

Specifications

Military Standard Part No.	MS3367-6
Temperature Rating	-40°F to 185°F
Flammability Rating	UL 94 V-2

Tooling

Application Tools	ERG120, WT197
-------------------	---------------

Packaging

T&B Order Multiple	500
Package in Units	500
Package Type	Bulk
T&B Sold in UOM	Each

T&B Weight Per UOM	2.26 lbs. per 100
--------------------	-------------------

Application Support

T&B Sales Drawings	wsd-000280
--------------------	------------

Overview	Available on Website
----------	----------------------

Material Selection Guide	Available on Website
--------------------------	----------------------

Available Colors	Available on Website
------------------	----------------------

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com