



Ty-Rap®

**Extra High Temperature
T&B Catalog Number:**

TYHT23M
78621095267
Active

**UPC Number:
Status:
Description:**

Cable Tie 18lb 4" Light Green High-Temperature Nylon with Stainless Steel Locking Device

Features

Oval low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time. Because there are no notches, Ty-Rap ties provide an infinite number of locking positions while fastening the tie at the precise bundle diameter needed.

The Turned-up Tail orients the tie for easy assembly, making the ties easier to pick up on a flat surface. The No-Slip Tail provides easy grip during tensioning. Ty-Rap ties feature a unique friction surface designed to reduce slippage during installation.

Smooth, notchless body reduces stress concentration points under tension, making the tie stronger and lower profile than notched body ties. Ribbed and Stippled body grips the bundle and prevents slippage. Rounded edges protect insulation, preventing sharp edges from damaging cables.

General

Material	Nylon 4.6 High Temperature
Color	Light Green

Dimension Information

Nominal Length (inches)	4
Length (inches)	3.62
Width (inches)	.093
Max. Wire Bundle Diameter (inches)	.625

Specifications

Temperature Rating	-40°F to 302°F
Flamability Rating	UL 94 V-2

Tooling

Application Tools	ERG50, WT1-TB
-------------------	---------------

Packaging

T&B Order Multiple	1000
T&B Inner Pack	1000
Package in Units	10000
Package Type	Bulk
T&B Sold in UOM	Each

T&B Weight Per UOM 0.07 lbs. per 100

Application Support

T&B Sales Drawings wsd-000156

Overview Available on Website

Material Selection Guide Available on Website

Certifications

RoHS Compliance Yes

Certifications



For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com