



# Sta-Kon®

**Locking Fork Terminal**  
**T&B Catalog Number:**

**UPC Number:** 14RB-6FLX  
**Status:** 78621080653  
**Description:** Active

Expanded Insulated Vinyl Locking Fork Terminal For Wire Range 18-14  
 Stud Size #6, Blue

**WEB\_USE**

US Cutsheet PDF Catalog Link <http://www-public.tnb.com/contractor/docs/stakon.pdf>

**Features**

Locking fork terminals have a specially designed tongue that lets them go on like a fork and stay on like a ring.

**General**

Insulation Type	Expanded Insulated Vinyl
Terminal Series	RB
Material	Copper
Finish	Electro -Tin Plated
Color	Blue
Wire Range	18-14
Stud Size	#6

**Dimension Information**

Maximum Insulation (inches)	.200
Stock Thickness	.03
A (inches)	.97
B (inches)	.31
C (inches)	.27
M (inches)	.81

**Specifications**


Temperature Rating	105°C
Voltage Rating	600V
Flammability Rating	UL 94 V-0

**Tooling**

Tool Charts	Available on Website
Application Tools	ERG4001, ERG4003, WT145C, WT2000, WT112M, WT145C
Recommended Tool	ERG4001

**Packaging**

T&B Order Multiple	100
T&B Inner Pack	100
Package in Units	500
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	0.28 lbs. per 100
Alternate Package Qty	RB2207-200



## Application Support

T&B Instruction Sheets

Overview Available on Website

Wire Guide Tables Available on Website

## Certifications

RoHS Compliance Yes

## Certifications



File Nbr:  
E9809

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com