



# T&B<sup>®</sup>

## Liquidtight Flexible Cord & Cable Fittings T&B Catalog Number:

**UPC Number:** 4960NM  
78621079749  
**Status:** Active  
**Description:**

1/2 in. 90 degree nylon Ranger liquidtight cord connector, cord range .125-.375

### Features

- Extended range with superior strain relief.
- Reduced overall size, fits into tighter spaces.
- Gland nut designed to restrict cable bending.

### Application

- Provide a means for passing a cord cable into an enclosure through a bulkhead
- Suitable for Ordinary, Wet or Dry locations.

### General

**Material** Nylon  
**Cord and Cable Types** S, SO, SV, ST, STD, SJ, SJO, SJT, SJTO, SVD

### Dimension Information

**Hub Size (inches)** 1/2  
**Dimension A (inches)** 1 7/32  
**Dimension B (inches)** 1 1/4  
**Dimension C (inches)** 5/8  
**Cord Range (inches)** .125-.375  
**Throat Diameter (inches)** 0.55

### Specifications

**3dmodel** Available on Website

### Packaging

**T&B Inner Pack** 25  
**Package in Units** 50  
**T&B Sold in UOM** Each  
**T&B Weight Per UOM** 6.7 lbs. per 100

### Application Support

**T&B Instruction Sheets** ta00927-tb2  
**Product Overview** Available on Website  
**Specifications** Available on Website  
**Portable Cord Selection Table** Available on Website

### Certifications

**RoHS Compliance** Yes

## Certifications



File Nbr:  
E 13938

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)