

# SACC-MS-17PCON SCO

Order No.: 1559602

<http://eshop.phoenixcontact.co.uk/phoenix/treeViewClick.do?UID=1559602>

Sensor/actuator connector, male connector, straight, 17-pos., M12 SPEEDCON, metal knurl, Piercecon®, maximum cable diameter of 8.2 mm



## Commercial data

EAN	 4 046356 314831
Pack	1
Customs tariff	85366990
Gross weight in pieces	34.80 g
Country of Origin	DE
Catalog page information	Page 19 (C-4-2013)

## Product notes

WEEE/RoHS-compliant since:  
07/09/2007



Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

## Technical data

### Dimensions

Wrench size, union nut	13 mm
External diameter	5.4 mm ... 8.2 mm
Stripping length of the sheath	≥ 60 mm

**Ambient conditions**

Ambient temperature (operation)	-25 °C ... 85 °C (Plug / socket)
Degree of protection	IP67

**General**

Rated current at 40°C	1.5 A
Rated voltage	30 V
Number of positions	17
Contact resistance	≤ 5 mΩ
Insulation resistance	≥ 100 MΩ
Coding	A - standard
Standards/regulations	M12 connector IEC 61076-2-101
Status display	No
Surge voltage category	II
Pollution degree	3
Connection method	Piercecon® fast connection
Conductor cross section	0.14 mm <sup>2</sup>
AWG conductor cross section	26
Wire diameter including insulation	0.95 mm ... 1.05 mm
Frequency of connections between conductors of the same cross section	≥ 5
Wire insulation material	PUR/PVC
Structure of individual litz in acc. with VDE 0295 / smallest wire diameter	VDE 0295 Class 6
Insertion/withdrawal cycles	≥ 100
Torque	0.4 Nm (M12 knurl)

**Material**

Inflammability class according to UL 94	V0
Contact material	CuZn
Contact surface material	Ni/Au
Contact carrier material	PA
Material of grip body	Zinc die-cast, nickel-plated
Material, knurls	Zinc die-cast, nickel-plated
Sealing material	FKM

## Certificates



Certification GOST

Certifications applied for:

Certification Ex:


## Accessories

Item	Designation	Description
<b>Cable/conductor</b>		
1441545	SAC-17P-100,0-PVC/0,14	Sensor/Actuator cable, 17-position, PVC, Black RAL 9005, Free cable end, on Free cable end, Cable length: 100 m
<b>Protection and sealing elements</b>		
1430873	PROT-M12 FS-PA-CHAIN	M12 sealing cap made of plastic with fixing band, for sensor cables, for free M12 sockets
<b>Tools</b>		
1212487	MICROFOX-SP-1	Electronic diagonal cutter, tapered head, without chamfer, with opening spring, non-reflective phosphate-treated surface, punched version
1208432	SAC BIT M12-D15	Nut for assembling sensor/actuator cables with M12 connector and for M12 connectors with QUICKON fast connection technology, for 4 mm hexagonal drive
1208429	TSD 04 SAC	Torque screwdriver, with preset torque of 0.4 Nm and 4 mm hexagonal drive for M12 connectors
1212224	TSD-M 1,2NM	Torque screw driver, accuracy as per EN ISO 6789 standard, adjustable from 0.3 - 1.2 Nm
1212600	TSD-M SAC-BIT ADAPTER	Adapter bit for TSD-M...torque tools, E6.3-1/4" drive with 4 mm hexagon to accommodate SAC bits

**Drawings**


Dimensioned drawing

M12 x 1 plug, straight



Schematic diagram

Pin assignment M12 male connector, 17-pos., male side view



**Address**

PHOENIX CONTACT Ltd  
Halesfield 13  
Telford / Shropshire / TF7 4PG,England  
Phone 01952 681 700  
Fax 01952 681 799  
<http://www.phoenixcontact.co.uk>



Phoenix Contact Ltd.  
Technical modifications reserved;