

SACC-M12-SCO NUT

Order No.: 1552243




<http://eshop.phoenixcontact.co.uk/phoenix/treeViewClick.do?UID=1552243>

M12 SPEEDCON housing screw connection for M12 female inserts, with O-ring, for all SPEEDCON-capable THR and wave soldering contact carriers



Commercial data

EAN	 4 046356 162111
Pack	60
Customs tariff	85389099
Gross weight in pieces	6.40 g
Country of Origin	DE
Catalog page information	Page 258 (C-2-2013)

Product notes

WEEE/RoHS-compliant since:
29/09/2006



Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
---------------------------------	------------------


General

Mounting type	M12 x 1
---------------	---------

Material

Material, knurls	Nickel-plated brass
Material	Zinc die-cast (nickel-plated)
Sealing material	EPDM

Certificates



Certification


GOST

Certifications applied for:

Certification Ex:

Drawings

Dimensioned drawing



Address

PHOENIX CONTACT Ltd
Halesfield 13
Telford / Shropshire / TF7 4PG,England
Phone 01952 681 700
Fax 01952 681 799
<http://www.phoenixcontact.co.uk>



Phoenix Contact Ltd.
Technical modifications reserved;