


VS-BH-M12FSX-10G-RJ45/90

Order No.: 1404548

<http://eshop.phoenixcontact.co.uk/phoenix/treeViewClick.do?UID=1404548>Control cabinet feed-through, M12, 8-pos., X-coded to RJ45 socket,
socket input 90°, IP65/67**Ethernet****Commercial data**

EAN	 4 046356 699419
Pack	1
Customs tariff	85366990
Gross weight in pieces	36.52 g
Country of Origin	DE
Catalog page information	Page 94 (C-2-2013)

Product notesWEEE/RoHS-compliant since:
15/09/2011

Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

Technical data**Mechanical characteristics**

Number of positions	8
Insertion/withdrawal cycles	≥ 100
Cable exit	angled
Color	black

Ambient conditions

Ambient temperature (operation)	-25 °C ... 85 °C
Degree of protection	IP65/67

Material data

Inflammability class according to UL 94	V0
Housing material	PA
Contact material	Copper alloy

Electrical characteristics

Number of positions	8
Nominal voltage U_N	60 V
Nominal current I_N	0.5 A
Transmission characteristics (category)	CAT6 _A
Rated current	1 A

Certificates


Certification

Certifications applied for:

Certification Ex:

Drawings


Dimensioned drawing



Panel cutout

Panel cutout

Circuit diagram



Address

PHOENIX CONTACT Ltd
Halesfield 13
Telford / Shropshire / TF7 4PG,England
Phone 01952 681 700
Fax 01952 681 799
<http://www.phoenixcontact.co.uk>



Phoenix Contact Ltd.
Technical modifications reserved;