

Capacitor, ceramic, 15 pF, +/-5% Tol, 100V, C0G



Dimensions (in)		
Symbol	Dimension	Tolerance
D	0.1	MAX
L	0.17	MAX
LL	1	MIN
F	0.02	NOM
K	0.02	NOM

Notes:

-Lead length shown is for parts supplied in bulk. See packaging specifications for lead lengths when not provided in bulk

General Information	
Supplier:	KEMET

Specifications	
Capacitance:	15 pF
Temperature Coefficient:	C0G
Voltage:	100V
Tolerance:	+/-5%
Body Type:	Axial Conformal
Lead Type:	Standard Leads
Termination Type:	Tin (Sn)

Packaging Specifications	
Package Kind:	T&R
Package Type:	Standard
Package Quantity:	5000