



Item # 78SH1, Classic II Foot Switch

- Cast aluminum body and treadle With steel base plate and nonskid base pad.
- All models single stage momentary contact.
- Single 3/4"-14 NPT threaded conduit entry is standard.
- Special Dual 1/2"-14 NPT threaded conduit entry and metric sizes available to the O.E.M. on special order.
- Scaled down cost effective size, ideally suited for portable equipment and other medium duty applications
- Full shield models are painted Alert Orange

Specifications

Features	<ul style="list-style-type: none"> • Driptight • Dusttight • Watertight • Oiltight
Description	Momentary
Type	Full Shield
Circuit	SPDT
Form	C
Electrical Rating	20 A 125-250 VAC 1 H.P. 125-250 VAC Heavy pilot duty 250 Vac max.
Construction/Standards	Nema Type 1, 2, 4 & 13 UL Enclosure 1, 2, 4 & 13 CSA Enclosure 1, 2, 4 & 13 EN 60529 Degree of Protection IP569
Size	7 1/4 x 6 1/4 x 5 1/2 Inch
Weight	2 3/4 lbs