

MODEL TL-2200



International size reference: C, ER26500

TECHNICAL DATA

(Typical values @+25°C for batteries stored for one year or less)



■ Nominal capacity @ 2 mA, to 2V	7.2 Ah
■ Rated voltage	3.6 V
■ Maximum recommended continuous current	230 mA
■ Maximum pulse current capability	400 mA
■ Weight	50.5g (1.78 oz)
■ Volume	26 cc
■ Operating temperature range	-55°C to +85°C
■ U.L. Component Recognition, MH 12193	

TADIRAN LITHIUM BATTERIES



AVAILABLE TERMINATIONS

SUFFIX- /S STANDARD	15-5120-21500
SUFFIX- /T SOLDER TABS	15-5120-31500



LITHIUM XTRA

Note: Any presentations in this data sheet concerning performance are for information purpose only and are not construed as warranties either expressed or implied, of future performance. Rev. B 04/03