



Nothing but **HEAVY DUTY**™

Power Tools

Hand Tools

Instruments

Accessories

Parts & Service



Step Drill Bit, 12 Hole, 3/16" to 7/8" by 1/16"

48-89-9130

★★★★★ Be the first to [Write a Review](#)

OVERVIEW

DETAILS

OPTIONS

REVIEWS



PRODUCT DETAILS

FEATURES	SPECIFICATIONS
✓ Single Cutting Edge provides true round holes every time	Shank 3/8"
✓ High Speed Steel Make-up is ideal for cutting into stainless steel, aluminum, brass, copper, plastic and more	Type Step Drill Bits
✓ Black Oxide Finish resists corrosion for longer life	Coating Black Oxide
✓ Speed Start Tip starts fast and reduces the risk of bit walking	Size 3/16" - 7/8"
✓ Laser Etched Markings for fast, easy hole size identification	Number of Steps 12
✓ 3-Flat Shank prevents bit from slipping in the chuck	Increments 1/16
	Application Metal Plastic Wood

Overview

Our line of step drill bits far surpasses the competition. With our single cutting edge design, you will have more control and a cleaner finish. Made of high speed steel, these new step drill bits are durable and designed to drill through most metals. The black oxide finish prevents

corrosion and has great capacity to work with drilling lubricants. The new speed start tip prevents bit walking and allows faster penetration. With laser etched markings you will always know your hole sizes...no guess work! Finally, the 3-flat shank prevents slipping in the chuck.

Item/Cat #	Size	Number of Steps	Increments	Shank
48-89-9130	3/16" - 7/8"	12	1/16	3/8"