



GREENLEE. MADE FOR THE TRADE![™]
A Textron Company

Products ▾

Support ▾

Resources ▾

Promotions ▾

Where to Buy ▾

SEARCH

GO

Supplier Center ▾

Distributor Center ▾

[VDV Tools](#) > [VDV Strippers](#) > [General Purpose](#) > STRIPPER 30-20 AWG PP RETAIL CARD

STRIPPER 30-20 AWG PP RETAIL CARD

Cat No: **PA1118** UPC No: **769328111736**



Description

- Head of tool and handles designed at optimum 22° angle to prevent awkward wrist bends
- Spring-loaded open
- Contoured wire stripping areas precision ground for accuracy
- Non-scoring strip and smooth wire cutting
- Features screw cutter and wire loops embedded in frames
- Built-in safety lock
- Gripping jaws on front of tool
- PA1117 will work on Romex household cable
- Not for use on steel or armored wire and cable

Specification

- Application : Strips 30-20 AWG Wire And Cable
- Depth : 0.650 IN (17.000 MM)
- Jaw Type : Gripping
- Overall Length : 7.100 IN (180.000 MM)
- Stripping Range : 30 - 20 AWG (0.050 - 0.500 SQ-MM)
- Type : GripP 20
- Weight : 6.500 OZ (185.000 GM)
- Width : 2.250 IN (57.000 MM)