

PA44WP/12P

12 Pole pillar terminal block with wire protector



Product Image
Coming Soon


PRODUCT SPECIFICATIONS

| | |
|-----------------------------------|------------------------|
| Accessories available | PA296 PA228 PA52 PA197 |
| Number of poles | 12 |
| Terminal material | Brass |
| Terminal type | Wire Protected |
| Body material | Natural polyamide |
| UL94 rating | UL94V2 |
| Base type | Standard |
| Max conductor size (Sq mm) | 4 |
| Min conductor size AWG | 14 |
| Max conductor size AWG | 10 |
| Max current (A) | 32 |
| Max voltage (V) | 750 |
| Minimum temp rating °C | -5 |
| Max temp rating °C | 110 |
| Pitch (mm) | 12 |
| Height (mm) | 20 |
| Width (mm) | 23 |
| Length (mm) | 139.3 |
| Diameter (mm) | 37 |