

**SOLID PC 3828 13 G**



Sample photo

**Order symbol:** PC 3828 13 G  
**Product nbr:** 5330363  
**Description:** Enclosure, PC  
**Remarks:** Grey cover

**EAN:** 6418074005564  
**El. number:**  
Finland: 3423717  
Italy: 7401050  
Sweden: 2539422  
Norway:

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
<b>mm:</b>		378	278	130	Ingress Protection (EN 60529): IP 66/67
<b>inch:</b>		14.9	10.9	5.1	Impact Resistance (EN 62262): IK 08/09
<b>Materials:</b>					Electrical insulation: Totally insulated
<b>Material:</b>		Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): Yes
<b>Base colour:</b>		RAL 7035			UV resistance: UL 508
<b>Cover colour:</b>		RAL 7035			Flammability Rating (UL 746 C 5): UL 746C 5V
<b>Cover screws material:</b>		Polyamide			Glow Wire Test (IEC 695-2-1) °C: 960
<b>Cover screws colour:</b>		Grey			NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12
<b>Gasket material:</b>		Polyurethane			
<b>Temperatures:</b>					<b>Certificates:</b>
<b>Short term:</b>		-40 ... 120 °C			Underwriters Laboratories
<b>Continuous:</b>		-40 ... 80 °C			Fimko
<b>Short term:</b>		-40 ... 250 °F			Europe EN 62208: 2003
<b>Continuous:</b>		-40 ... 175 °F			
<b>Accessories:</b>					
EKPVT		Mounting plate			
EKPXT		Mounting plate Pertinax			
EKV 22		DIN-35 Mounting rail			
EKV 32		DIN-35 Mounting rail			
EKPZR		Extension frame			

