

SOLID PC 3828 13 G-2FSH



Sample photo

Order symbol: PC 3828 13 G-2FSH
Product nbr: 2539521
Description: Enclosure, PC
Remarks: Grey hinged cover

EAN: 6418074052742
EI. number:
 Finland: 3435730
 Sweden: 2539521
 Norway:

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		378	278	130	Ingress Protection (EN 60529): IP 65
inch:		14.9	10.9	5.1	Impact Resistance (EN 62262): IK 08/09
Materials:					Electrical insulation: Totally insulated
Material:		Polycarbonate		Halogen free (DIN/VDE 0472, Part 815): Yes	
Base colour:		RAL 7035		UV resistance: UL 508	
Cover colour:		RAL 7035		Flammability Rating (UL 746 C 5): UL 746C 5V	
Cover screws material:		Polyamide		Glow Wire Test (IEC 695-2-1) °C: 960	
Cover screws colour:		Grey		UL Type: UL TYPE 1, 3, 3S, 12	
Gasket material:		Polyurethane			
Temperatures:					Certificates:
Short term:		-40 ... 120 °C		Underwriters Laboratories	
Continuous:		-40 ... 80 °C		Fimko	
Short term:		-40 ... 250 °F		Europe EN 62208: 2003	
Continuous:		-40 ... 175 °F		UL Canada	
Accessories:					Gost R
EKPVT		Mounting plate			
EKPXT		Mounting plate Pertinax			
EKV 22		DIN-35 Mounting rail			
EKV 32		DIN-35 Mounting rail			
EKPZR		Extension frame			

