

**SOLID PC 3828 13 T-2FSH**



Sample photo

**Order symbol:** PC 3828 13 T-2FSH  
**Product nbr:** 2539551  
**Description:** Enclosure, PC  
**Remarks:** Transparent hinged cover

**EAN:** 6418074052865  
**EI. number:**  
 Finland: 3435754  
 Sweden: 2539551  
 Norway:

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
<b>mm:</b>		378	278	130	Ingress Protection (EN 60529): IP 65
<b>inch:</b>		14.9	10.9	5.1	Impact Resistance (EN 62262): IK 08/09
<b>Materials:</b>					Electrical insulation: Totally insulated
<b>Material:</b>		Polycarbonate		Halogen free (DIN/VDE 0472, Part 815): Yes	
<b>Base colour:</b>		RAL 7035		UV resistance: UL 508	
<b>Cover colour:</b>		Clear transparent		Flammability Rating (UL 746 C 5): UL 746C 5V	
<b>Cover screws material:</b>		Polyamide		Glow Wire Test (IEC 695-2-1) °C: 960	
<b>Cover screws colour:</b>		Grey		UL Type: UL TYPE 1, 3, 3S, 12	
<b>Gasket material:</b>		Polyurethane			
<b>Temperatures:</b>					<b>Certificates:</b>
<b>Short term:</b>		-40 ... 120 °C		Underwriters Laboratories	
<b>Continuous:</b>		-40 ... 80 °C		Fimko	
<b>Short term:</b>		-40 ... 250 °F		Europe EN 62208: 2003	
<b>Continuous:</b>		-40 ... 175 °F		UL Canada	
<b>Accessories:</b>					Gost R
EKPVT		Mounting plate			
EKPXT		Mounting plate Pertinax			
EKV 22		DIN-35 Mounting rail			
EKV 32		DIN-35 Mounting rail			
EKPZR		Extension frame			

