

SOLID PC 5628 13 G



Sample photo

Order symbol: PC 5628 13 G
Product nbr: 5330364
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074005601
EI. number:
 Finland: 3423721
 Italy: 7401060
 Sweden: 2539426
 Norway:

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

| Dimensions: | | Length | Width | Height | Rating: |
|-------------------------------|--|-------------------------|-------|--|--|
| mm: | | 558 | 278 | 130 | Ingress Protection (EN 60529): IP 66/67 |
| inch: | | 22.0 | 10.9 | 5.1 | Impact Resistance (EN 62262): IK 08/09 |
| Materials: | | | | | Electrical insulation: Totally insulated |
| Material: | | Polycarbonate | | Halogen free (DIN/VDE 0472, Part 815): Yes | |
| Base colour: | | RAL 7035 | | UV resistance: UL 508 | |
| Cover colour: | | RAL 7035 | | Flammability Rating (UL 746 C 5): UL 746C 5V | |
| Cover screws material: | | Polyamide | | Glow Wire Test (IEC 695-2-1) °C: 960 | |
| Cover screws colour: | | Grey | | NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12 | |
| Gasket material: | | Polyurethane | | | |
| Temperatures: | | | | | Certificates: |
| Short term: | | -40 ... 120 °C | | Underwriters Laboratories | |
| Continuous: | | -40 ... 80 °C | | Fimko | |
| Short term: | | -40 ... 250 °F | | Europe EN 62208: 2003 | |
| Continuous: | | -40 ... 175 °F | | | |
| Accessories: | | | | | |
| EKTVT | | Mounting plate | | | |
| EKTXT | | Mounting plate Pertinax | | | |
| EKV 22 | | DIN-35 Mounting rail | | | |
| EKV 50 | | DIN-35 Mounting rail | | | |
| EKTZR | | Extension frame | | | |

