

Datasheet

V55-002 Visionlink™ Remote Control Link Eye (Sky & Sky+ compatible)

- New slim line design for easy behind the TV fitting
- Fully screened with reliable F connector input / IR return connection
- IEC TV male on flexible cable for TV connection
- L.E.D power indicator
- Low current consumption

The new V55-002 Visionlink^(TM) has been updated to a new slim-line housing making it easy to fit behind an LCD TV mounted on a slim fixed LCD wall bracket. The extra small "Eye", only 9mm high, has been designed to be discretely positioned on the front escutcheon, edge or rear of the TV so as to be virtually invisible.



Model	V55-002
Forward Path Pass Frequency	80-862MHz
RF Insertion loss	<1dB
IR Carrier Frequency	7MHz
Voltage	9V
Current Consumption	8mA
Power Indication	Red L.E.D
Input Cable Connector	F female
Output Cable Connector	IEC TV Male on 150mm flylead
IR "Eye" Flylead Length	900mm
IR "Eye" Dimension L x W x H	25 x 15 x 9mm
IR Compatibility	Sky™, Sky+™
Screen Compatibility	LCD, LED, Plasma
Dimensions of Body L x W x H	54 x 27 x 20mm excludes connector
Length including input connector & output strain relief	87mm
Supplied Accessories	Double sided adhesive pad for "eye" Double sided adhesive pad for body
Packing	White labelled carton 1 pc Outer carton content 200pcs
Weight	0.09kg

Note: Sky and Sky+ are trademarks of British Sky Broadcasting

In the interests of continued product improvement and development we reserve the right to change specifications, design and dimensions without prior notice. Details correct at date of publication 25/10/2011

Vision Products (Europe) Ltd, Unit 5 Redbourne Park, Liliput Road, Brackmills, Northampton NN4 7DT

Tel: 01604 662748 Fax: 01604 662746 Email: technical@vision-products.co.uk

E&OE ©2012 Vision Products (Europe) Ltd

Company Reg No: 05044212

www.vision-products.co.uk