

Specification of AC adapter

		Discontinue model PW-4007-EC-E	Alternate adapter PW-C0725-W1-E
Input			
Input voltage AC		100 to 120 V	100 to 240 V
Frequency		47 to 63 Hz	47 to 63 Hz
Output			
Output voltage DC		7.0 V	7.0 V +/-5%
Output current		2.0 A Max.	2.5 A Max.
Regulation/EMI			
Regulation	Japan	PSE	PSE , J60950
	USA	UL1950 CSA C22.2 NO.950	UL, cUL UL60950
	Canada	UL1950 CSA C22.2 NO.950	UL, cUL UL60950
	Taiwan	BSMI	BSMI
EMI	Japan	VCCI / FCC ClassB	CE / FCC ClassB
	USA	VCCI / FCC ClassB	CE / FCC ClassB
	Canada	VCCI / FCC ClassB	CE / FCC ClassB
	Taiwan	VCCI / FCC ClassB	CE / FCC ClassB
Temperature character			
Operating temperature range		0 to +40 deg C	0 to +40 deg C
Storage temperature range		-20 to +60 deg C	-20 to +80 deg C
Case			
Dimensions (LxWxH)		104 x 43 x 33mm	77.5 x 51.8 x 39.2 mm
Mass		Approx. 160 g	Approx. 165 g
AC plug			
Type of connector		2pin AC inlet	Direct plug-in
DC			
DC cable length		1850mm	1500mm
DC plug dimensions (O.D / I.D. / length)		5.5mm / 2.1mm / 9.5mm	5.5mm / 2.1mm / 9.5mm
DC plug polar		O.D.:+ / Center:-	O.D.:+ / Center:-

Model indication

SII

I.T.E POWER SUPPLY SII P/N:PW-C0725-W1

电源适配器 / 電源適配器

Model (型号/型號) :STD-07025V (适用于资讯类产品)

Input (输入/輸入) :100-240V~47-63Hz 0.48A MAX

Output (输出/輸出) :7V=2.5A 17.5W MAX

CAUTION:Risk of electric shock.
Dry location use only.
Indoor use only.

警告!屋内専用,小心电击,干燥地区使用

KTL SU10454-10001

품명:직류전원장치
 모델명:STD-07525V
 제품정격:(I/P:100-240V;47-63Hz;0.48A)
 (O/P:7.0V;2.5A)
 제조자:BoayYang Electronics Co., Ltd.
 제조공장:Adapter Technology Co., Ltd.
 A/S연락처:02-565-8006
 제조년월:
 최저소비효율기준 인증 제품

RoHS

EFFICIENCY LEVEL

60JJ
E225703
US LISTED

N148
V06812

JET
 세이코인스툴株式会社

I/P:AC 100-240V 50/60Hz 39-49VA 0.48A
 O/P:DC7.0V 2.5A

S/N:


D/C:
ID NO. A
CPC

精工电子有限公司 台湾销售商:台精精密股份有限公司
 Seiko Instruments Inc. MADE IN CHINA 中国制造/中國製造


R33154

Dimensions

Discontinue model : PW-4007-EC-E



Alternate model : PW-C0725-W1-E



Unit : mm