

Main

Commercial Status	Commercialised
Product or component type	Industrial Control Transformer
Product certifications	CE CSA UL listed
NEMA degree of protection	Not rated (open device)
Insulation temperature	221 °F (105 °C)
Network number of phases	1 phase
Rated power in VA	50 VA
Primary voltage	240 x 480 V
Secondary voltage	24 V
Temperature rise	55 °C
Electrical connection	Screw clamp terminals
Range of product	T

Ordering and shipping details

Category	16200 - 9070 T (NOT TF) 50-200VA
Discount Schedule	CP8
GTIN	00785901904939
Nbr. of units in pkg.	1
Package weight(Lbs)	2.56
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	MX

Contractual warranty

Period	10 years
--------	----------