



PROLITE[®] STEREO-ZOOM 4.5 BINOCULAR MICROSCOPE - LABORATORY BASE

SKU# TKSZ-L

Prolite[®] Stereo-Zoom 4.5 Binocular Microscope featuring Large (22mm) 10X Eyepieces. Standard Magnification Range of 7 - 45x (up to 270X with options). 0.5x Auxiliary lens included for increased working distance. **Laboratory style base assembly included.** Compatible with all Micro-Lite[®] Illuminators. **ESD Safe**

4 Light Source Options Available

- **FL1000** | Flicker-Free Dimmable Fluorescent
- **LV2000** | High Intensity Dimmable LED
- **FL3000-A** | "Annular" Fiber Optic
- **FL3000-D** | "Dual-Point" Fiber Optic

PRODUCT DESCRIPTION

Prolite[®] Stereo-Zoom 4.5 Binocular Microscope featuring Large (22mm) 10X Eyepieces. Standard Magnification Range of 7 - 45x (up to 270X with options). 0.5x Auxiliary lens included for increased working distance. **Laboratory style base assembly included.** Compatible with all Micro-Lite[®] Illuminators. **ESD Safe**

4 Light Source Options Available

- **FL1000** | Flicker-Free Dimmable Fluorescent
- **LV2000** | High Intensity Dimmable LED
- **FL3000-A** | "Annular" Fiber Optic
- **FL3000-D** | "Dual-Point" Fiber Optic

SPECIFICATIONS

Name	Prolite [®] Stereo-Zoom 4.5 Binocular Microscope - Laboratory Base
SKU	TKSZ-L
Product Line	Prolite [®]
Magnification	7 - 45x (up to 270X with options)
Mounting Style	Lab Style
Voltage	120 Volt
ESD Safe	Yes