



**GREEN-LITE™ - 6" ROUND LED MAGNIFIER - 43" REACH -
SCREW DOWN BASE**

SKU# 42300-4

Equipped with next generation, surface mount LEDs, these innovative designs create the new standard for illuminated magnifiers. Your investment in new technology quickly pays for itself through energy savings. Made in the USA.

PRODUCT DESCRIPTION

Equipped with next generation, surface mount LEDs, these innovative designs create the new standard for illuminated magnifiers. Your investment in new technology quickly pays for itself through energy savings. Made in the USA.

Lighting Features

- Highest lumen output in a lighted magnifier
- Reduced glare, heat and energy consumption
- Multi-angle LEDs for shadowless lighting at a full range of focal lengths and heights
- User controlled LED groups shine desired level of light exactly where required
- Superb dimming software via convenient, reliable membrane switch

Optical Features

- Precision ground, optical grade glass
- Largest lenses in the industry
- Standard 4 diopter (2x) lens – O.C. White exclusive
- Optional 5 diopter (2.25x) lens available
- New 6" round lens with 44% more viewing area than old style 5" round lens – an O.C. White exclusive at no extra charge

Electrical Features

- Low voltage (15-24v) power supplies are auto-switchable with worldwide approvals
- Plug in around the world by simply switching the end power cord
- Energy Star compliant (each unit uses 8 watts maximum)
- Auto shut off at 4 hour intervals to prevent energy waste while users are away

Mechanical Features

- High quality die cast aluminum shades and all steel arm components for ESD safety
- Patented "Elite" arms are slim but have the greatest holding power of any arm of this type in the world
Virtually "maintenance zero"

SPECIFICATIONS

Name	Green-Lite™ - 6" Round LED Magnifier - 43" Reach -Screw Down Base
SKU	42300-4
Product Line	Green-Lite™
Magnification	2x (4 Diop) 2.25x (5 Diop) Optional
Reach	43"
Mounting Style	Screw Down Base
Voltage	120 Volt - 240 Volt
ESD Safe	Yes