



MICRO-LITE® 150W HALOGEN LIGHT SOURCE WITH DUAL GOOSENECK FIBER OPTIC LIGHT GUIDE - .565" ID BORE

SKU# FL3000-D

Micro-Lite® 150w Halogen Light Source with Dual Gooseneck Fiber Optic Light Guide. Included standard are Focusing Spot lenses for the Dual Gooseneck. Features an Integral IR Filter for Cold Performance and long fiber life. Our standard model features a **.565" ID Bore**. All Metal Construction, and 120v (230v Available). **ESD Safe**

PRODUCT DESCRIPTION

Micro-Lite® 150w Halogen Light Source with Dual Gooseneck Fiber Optic Light Guide. Included standard are Focusing Spot lenses for the Dual Gooseneck. Features an Integral IR Filter for Cold Performance and long fiber life. Our standard model features a **.565" ID Bore**. All Metal Construction, and 120v (230v Available). **ESD Safe**

SPECIFICATIONS

Name	Micro-Lite® 150w Halogen Light Source with Dual Gooseneck Fiber Optic Light Guide - .565" ID Bore
SKU	FL3000-D
Product Line	Micro-Lite®
Voltage	120 Volt
ESD Safe	Yes