

Black Box Products

Cables > Computer & Data Cables



Bulk Standard RS-232 Cable, 4 Conductors (2 Pairs), 500-ft. (152.4-m)



Standard RS-232 cable for 50-foot data runs.

ECN04A-0500

Extended Double Diamond™ Warranty Available (Lifetime)

Product Highlights

- Can also be used for parallel transmissions up to 20 feet (6 m).
- Unshielded data cable.
- 22 AWG stranded construction.
- Guaranteed for life!

Details

Description

Bulk Standard RS-232 Cable, 4 Conductors (2 Pairs), 500-ft. (152.4-m)

Quick Facts

- Can also be used for parallel transmissions up to 20 feet (6 m).
- Unshielded data cable.
- 22 AWG stranded construction.
- Guaranteed for life!

Tech Spec

Technical Specifications for Bulk Standard RS-232 Cable, 4 Conductors (2 Pairs), 500-ft. (152.4-m):

Cable Type	— Gray PVC
Capacitance	— 50 pF/ft.
Conductor Gauge	— 22 AWG (7 x 30 AWG), stranded
Resistance	— Less than 16 ohms/1000 ft.
Shield	— None