

Black Box Products

Cables > Modular/Telephone Cables



RJ-11 Modular Cable, 6-Wire, Crossed-Pinning, 4-ft. (1.2-m)

Flat satin 6-wire cabling for voice and data.

EL06M-04

Extended Double Diamond™ Warranty Available
(Lifetime)

Product Highlights

- High-quality flat-satin cable for data and voice applications.
- Stranded conductor.
- All-purpose cables is for voice and data applications running up to 1 Mbps.
- Not recommended for Token Ring or Ethernet applications.
- 4-Wire also available.
- Guaranteed for life!

Details

Description

RJ-11 Modular Cable, 6-Wire, Crossed-Pinning, 4-ft. (1.2-m)

Quick Facts

- High-quality flat-satin cable for data and voice applications.
- Stranded conductor.
- All-purpose cables is for voice and data applications running up to 1 Mbps.
- Not recommended for Token Ring or Ethernet applications.
- 4-Wire also available.
- Guaranteed for life!

Tech Spec

Technical Specifications for RJ-11 Modular Cable, 6-Wire, Crossed-Pinning, 4-ft. (1.2-m):

| | |
|---------------------------|---|
| Cable Construction | — Gray flat satin, PVC |
| Conductor Gauge | — 28 AWG |
| Distance (Maximum) | — As per equipment specifications |
| Mutual Capacitance | — 22 pF/ft. |
| Resistance | — 45 ohms/1000 ft. |
| Connectors | — EL04MS, EL04M: 4-wire; — EL06MS, EL06M: 6-wire |