


Black Box Products

Datacom > Switches

ABC Dual Switch, DB25 and DB25 for RS-232, Chassis Style B



Two switches in one.

SW184A

Extended Double Diamond™ Warranty Available
(Lifetime)

Product Highlights

- This dual switch has one common port (C) with a DB25 connector and one common port (C) with an RJ-11, RJ-45, DB25, or 4-wire terminal strip.
- Each port (A or B) has two standard female connectors.
- Guaranteed for life!

Details

Description

ABC Dual Switch, DB25 and DB25 for RS-232, Chassis Style B

Quick Facts

- This dual switch has one common port (C) with a DB25 connector and one common port (C) with an RJ-11, RJ-45, DB25, or 4-wire terminal strip.
- Each port (A or B) has two standard female connectors.
- Guaranteed for life!

Further Details

Each switch includes two sets of ABC connectors on the back of the box. Turn the knob on the front panel to switch both sets to either the A or the B position simultaneously.

This switch also has two connectors for each switch position (A or B).

Switch two devices connected to port A or two devices connected to port B simultaneously.

This product works with:

- Gender Changers (FA402-R2, FA412-R2)
- DB25 Extension Cable (BC00701)

Tech Spec

Technical Specifications for ABC Dual Switch, DB25 and DB25 for RS-232, Chassis Style B:

Leads Supported	— Dual ABC 24 leads, leads 2–25 switched and Pin 1 tied common
MTBF	— 25,000 cycles
Relative Humidity	— Operating or Storage: Up to 95%, noncondensing
Temperature Tolerance	— Operating: 32 to 114° F (0 to 45° C);
Storage	— -40 to +176° F (-40 to +80° C)
Connectors	— (6) DB25; SW188A: (3) DB25, (3) 4-wire terminal strip
Size	— 3.5"H x 6"W x 6.3"D (8.9 x 15.2 x 16 cm)
Weight	— 1.5 lb. (0.7 kg)