

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [35547-0400](#)
Status: **Active**
Description: 6.35mm Tab Multiple Wire-to-Wire Male Housing, 4 Circuits

Documents:

3D Model	Product Specification PS-35546-002 (PDF)
Drawing (PDF)	Packaging Specification PK-35547-001 (PDF)
Product Specification PS-35546-001 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Housings
Series	35547
Application	Power, Wire-to-Wire
Product Name	N/A
UPC	800753127241

Physical

Circuits (maximum)	4
Gender	Male
Glow-Wire Compliant	No
Net Weight	6.520/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	10.80mm
Temperature Range - Operating	-40°C to +120°C

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-35547-001
Product Specification	PS-35546-001, PS-35546-002
Sales Drawing	SD-35547-001, SD-35547-002




image - Reference only

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

**Contains SVHC: No
Low-Halogen Status
Not Low-Halogen**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series

35547Series

Mates With

35546

Use With

35725 , 35452 , 35453