



**T&B<sup>®</sup>**

**Rigid/IMC Conduit Fittings-Hazardous Location  
T&B Catalog Number:**

**UPC Number:** GUAT24-TB  
**Status:** 78621098175  
**Description:** Active

3/4 in. GUAT Hazardous location Conduit Outlet Box, Box-Ductile Iron-Zinc Plated, Cover-Die Cast Aluminum, 5.3 cu.in.

**Features**

All hubs have a minimum of five full threads and integral bushing  
 All boxes are furnished with internal grounding screw.

**Application**

GUA boxes can be used for hazardous location conduit runs for the following: (1) Allows for mounting of fixture outlets when used with appropriate covers; (2) Provides easy access to wiring; (3) Provides junction in conduit for wire pulling and splices; (4) Changes direction in rigid conduit systems; (5) Attaches two or more pieces of conduit long runs; (6) Guards against damage to wires in rigid conduit.

**General**

**Material:** Ductile Iron  
**Finish:** Zinc Plated  
**Volume (cu.in.):** 5.3

**Dimension Information**

**Hub Size (inches):** 3/4  
**Dimension A (inches):** 2  
**Dimension B (inches):** 2 1/2  
**Dimension C (inches):** 7/8  
**Throat Diameter-Max (inches):** 0.810  
**Throat Diameter-Min (inches):** 0.755

**Specifications**

**3dmodel:** Available on Website

**Packaging**

**T&B Inner Pack:** 1  
**Package in Units:** 5  
**T&B Sold in UOM:** Each  
**T&B Weight Per UOM:** 218 lbs. per 100

**Notes**

**\*Note:** Class I, Div. 1&2, Groups C, D - Explosionproof  
**\*\*Note:** Class II, Div. 1, Groups E, F, G - Dust-Ignitionproof  
**\*\*\*Note:** Class III, Div. 1&2 - Raintight  
**\*\*\*\*Note:** NEMA 3, 4, 7 CD, 9 EFG - Wet Locations

**Certifications**

RoHS Compliance

No

**Certifications**



File Nbr:

E 202368

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com