


**FV110**

3 Pole screw to tab terminal block


**PRODUCT SPECIFICATIONS**

Accessories available	PA269
Number of poles	3
Tabs per pole	3
Tab size (mm)	6.3x0.8
Terminal material	Zinc-plated steel
Body material	Polyamide, glass fibre reinforced
UL94 rating	UL94V0
Max conductor size (Sq mm)	6
Min conductor size AWG	22
Max conductor size AWG	8
Max current (A)	40
Max voltage (V)	450
Minimum temp rating °C	-5
Max temp rating °C	150
Pitch (mm)	17.7
Height (mm)	24
Width (mm)	31.5
Length (mm)	81.3