

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [43025-0600](#)  
**Status:** **Active**  
**Overview:** Micro-Fit 3.0™ Connectors  
**Description:** Micro-Fit 3.0™ Receptacle Housing, Dual Row, 6 Circuits, Halogen Free

**Documents:**

|  |  |
|--|--|
| <a href="#">3D Model</a>                                   | <a href="#">Test Summary TS-43045-001 (PDF)</a>      |
| <a href="#">Drawing (PDF)</a>                              | <a href="#">RoHS Certificate of Compliance (PDF)</a> |
| <a href="#">Product Specification PS-43045 (PDF)</a>       | <a href="#">Product Literature (PDF)</a>             |
| <a href="#">Packaging Specification PK-43025-001 (PDF)</a> |  |




image - Reference only

**Agency Certification**

|     |           |
|-----|-----------|
| CSA | LR19980   |
| TUV | R72081037 |
| UL  | E29179    |

**General**

|                             |   |
|-----------------------------|---|
| Product Family              | Crimp Housings  |
| Series                      | <a href="#">43025</a>   |
| Application                 | Power, Wire-to-Board, Wire-to-Wire  |
| Comments                    | Polarized to Mating Part; Glow Wire Equivalent Part Number <a href="#">43025-0608</a> |
| Overview                    | <a href="#">Micro-Fit 3.0™ Connectors</a>   |
| Product Literature Order No | 987650-5984   |
| Product Name                | Micro-Fit 3.0™  |
| UPC                         | 800753683617  |

**Physical**

|                               |                 |
|-------------------------------|-----------------|
| Circuits (maximum)            | 6               |
| Circuits Detail               | 6               |
| Color - Resin                 | Black           |
| Flammability                  | 94V-0           |
| Gender                        | Female          |
| Glow-Wire Compliant           | No              |
| Keying to Mating Part         | None            |
| Lock to Mating Part           | Yes             |
| Material - Resin              | Nylon           |
| Net Weight                    | 0.570/g         |
| Number of Rows                | 2               |
| Packaging Type                | Bag             |
| Panel Mount                   | No              |
| Pitch - Mating Interface      | 3.00mm          |
| Polarized to Mating Part      | Yes             |
| Stackable                     | No              |
| Temperature Range - Operating | -40°C to +105°C |

**Electrical**

|                               |    |
|-------------------------------|----|
| Current - Maximum per Contact | 5A |
|-------------------------------|----|

**Material Info**

**Reference - Drawing Numbers**

|                         |   |
|-------------------------|---|
| Packaging Specification | PK-43025-001  |
| Product Specification   | PS-43045, RPS-43045-001, RPS-43045-003, RPS-43045-004 |
| Sales Drawing           | SDA-43025-****, SDES-43025-1000                       |
| Test Summary            | TS-43045-001  |

**EU RoHS**

**ELV and RoHS Compliant**  
**REACH SVHC Contains SVHC: No**  
**Low-Halogen Status Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[43025Series](#)

**Mates With**

Micro-Fit 3.0™ Plug Housing [43020](#). Micro-Fit 3.0™ Header [43045](#). Micro-Fit 3.0™ Test Plug [44242](#)

**Use With**

Micro-Fit 3.0™ Crimp Terminal [43030](#) , [46235](#) , [45773](#)

This document was generated on 11/11/2013

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**